



Thread code UECB	
Thread type	ACME
Major diameter [mm]	3.378...3.505
Minor diameter [mm]	1.910...2.250
Lead	2
Pitch	1
Starts	2
Thread per inch	25.4

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu ( $\pm 1.4570$ )		
				 <b>Nanotec</b> PLUG & DRIVE			Name	Date		
B	-	21.07.22	X T				DRN	L W	12.04.2018	THREADED SPINDLE
A	-	09.12.20	X T				CHKD	GYQ	12.04.2018	SCREW-ABA-UECB-200
REV	DESCRIPTION	DATE	DRN				APVD	P.R.	12.04.2018	