



Thread code: UEAI	
Thread type	ACME
Major diameter [mm]	3.378...3.505
Minor diameter [mm]	2.908...3.068
Lead	0.3048
Pitch	0.3048
Starts	1
Thread per inch	83.33

					Surface specification DIN ISO 1302	General tolerances DIN ISO 2768- mK	Work piece edge DIN ISO 13715	Scale: Material: SUS303Cu ( $\pm 1.4570$ )	
							Name	Date	
					DRN	X T	16.12.2022	THREADED SPINDLE SCREW-AAA-UEAI-500	
					CHKD	GYQ	16.12.2022		
REV	DESCRIPTION	DATE	DRN			APVD	P.R.	16.12.2022	