



| Thread code UQBN    |               |
|---------------------|---------------|
| Thread type         | ACME          |
| Major diameter [mm] | 9.398...9.525 |
| Minor diameter [mm] | 7.257...7.684 |
| Lead                | 1.5875        |
| Pitch               | 1.5875        |
| Starts              | 1             |
| Thread per inch     | 16            |

|     |             |          |     |  |   |  |                                  |   |                  |
|-----|-------------|----------|-----|--|---|--|----------------------------------|---|------------------|
|     |             |          |     |  | Surface specification<br>DIN ISO 1302       | General tolerances<br>DIN ISO 2768- mK | Work piece edge<br>DIN ISO 13715 | Scale:<br>Material: SUS303Cu ( $\pm 1.4570$ ) |                  |
|     |             |          |     |  | <b>Nanotec</b> <sup>®</sup><br>PLUG & DRIVE |  | Name                             | Date  | THREADED SPINDLE |
| A   | -           | 25.07.22 | X T |  |   | DRN                                    | X T                              | 29.04.2020                                    |                  |
| REV | DESCRIPTION | DATE     | DRN |  |   | CHKD                                   | GYQ                              | 29.04.2020                                    |                  |
|     |             |          |     |  |   | APVD                                   | P.R.                             | 29.04.2020                                    |                  |